

## D-Sub hood 09-pole top entry IP 67 black



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 09 67 009 0436                                                                |
| Specification      | D-Sub hood 09-pole top entry IP 67 black                                      |
| HARTING eCatalogue | <a href="https://harting.com/09670090436">https://harting.com/09670090436</a> |

### Identification

|                      |                  |
|----------------------|------------------|
| Category             | Hoods / Housings |
| Series               | D-Sub            |
| Identification       | IP67             |
| Type of hood/housing | Shell housing    |

### Version

|                         |               |
|-------------------------|---------------|
| Size                    | D-Sub 1       |
| Version                 | Top entry     |
| Number of cable entries | 1             |
| Cable entry             | 1x            |
| Cable fixing            | Cable clamp   |
| Locking type            | Screw locking |
| 2 parts                 | No            |
| Separable               | No            |

### Technical characteristics

|                                        |                          |
|----------------------------------------|--------------------------|
| Tightening torque                      | 0.4 Nm Fixing screws     |
|                                        | 0.4 Nm Cable clamp screw |
| Ambient temperature                    | -35 ... +120 °C          |
| Degree of protection acc. to IEC 60529 | IP67                     |
| Cable diameter                         | 6 ... 8 mm               |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |                                                                                                            |
|--------------------------------------|------------------------------------------------------------------------------------------------------------|
| Material (hood/housing)              | Thermoplastic                                                                                              |
| Colour (hood/housing)                | Black                                                                                                      |
| Length                               | 41 mm                                                                                                      |
| Width                                | 33.6 mm                                                                                                    |
| Height                               | 15.6 mm                                                                                                    |
| RoHS                                 | compliant with exemption                                                                                   |
| RoHS exemptions                      | 6(a)-I: Lead as an alloying element in steel for machining purposes containing up to 0,35 % lead by weight |
|                                      | 6(c): Copper alloy containing up to 4 % lead by weight                                                     |
| ELV status                           | compliant with exemption                                                                                   |
| China RoHS                           | 50                                                                                                         |
| REACH Annex XVII substances          | Not contained                                                                                              |
| REACH ANNEX XIV substances           | Not contained                                                                                              |
| REACH SVHC substances                | Yes                                                                                                        |
| REACH SVHC substances                | Lead                                                                                                       |
| ECHA SCIP number                     | ecef7555-f643-4ceb-a337-fc54762297f1                                                                       |
| California Proposition 65 substances | Yes                                                                                                        |
| California Proposition 65 substances | Lead                                                                                                       |
|                                      | Nickel                                                                                                     |

## Commercial data

|                                |                     |
|--------------------------------|---------------------|
| Packaging size                 | 100                 |
| Net weight                     | 19.115 g            |
| Country of origin              | Czechia             |
| European customs tariff number | 85389099            |
| GTIN                           | 5713140089136       |
| eCl@ss                         | 27440213 D-Sub hood |
| ETIM                           | EC001133            |
| UNSPSC 24.0                    | 39121416            |