

D-Sub crimp 15-pole male assembly



Image is for illustration purposes only. Please refer to product description.

Part number	09 67 015 5601
Specification	D-Sub crimp 15-pole male assembly
HARTING eCatalogue	https://harting.com/09670155601

Identification

Category	Connectors
Series	D-Sub
Identification	Standard
Element	Connector

Version

Termination method	Crimp termination
Gender	Male
Size	D-Sub 2
Connection type	PCB to cable Cable to cable
Number of contacts	15
Locking type	Fixing flange with feed through hole Ø 3.1 mm
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	0.09 ... 0.82 mm ²
Conductor cross-section [AWG]	AWG 28 ... AWG 18
Wire outer diameter	2.4 mm
Clearance distance	≥1 mm
Creepage distance	≥1 mm
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-55 ... +125 °C



Pushing Performance
Since 1945

Technical characteristics

Insertion force	≤50 N
Withdrawal force	≥4.5 N ≤33 N
Test voltage $U_{r.m.s.}$	1 kV
Isolation group	II ($400 \leq CTI < 600$)
Hot plugging	No

Material properties

Material (insert)	Thermoplastic resin, glass-fibre filled (PBTP) Shell: Plated steel
Colour (insert)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

Specifications and approvals

Specifications	DIN 41652 IEC 60807-3 CECC 75301-802
UL / CSA	UL 1977 ECBT2.E102079

Commercial data

Packaging size	100
Net weight	0.08 g
Country of origin	China
European customs tariff number	85366990
GTIN	5713140090897
eCl@ss	27440214 D-Sub coupler



Pushing Performance
Since 1945

Commercial data

ETIM	EC001136
UNSPSC 24.0	39121469