

D-Sub_CCH_S3_PP_PL



Image is for illustration purposes only. Please refer to product description.

Part number	09 67 025 0200
Specification	D-Sub_CCH_S3_PP_PL
HARTING eCatalogue	https://harting.com/09670250200

Identification

Category	Hoods / Housings
Series	D-Sub
Type of hood/housing	Shell housing
Description of hood/housing	Cover lockable

Version

Size	D-Sub 3
Version	Top/side entry
Cable entry	3x
Cable fixing	Cable clamp
Locking type	PushPull
2 parts	Yes
Separable	Yes
Details	An external InduCom cable clamp or a crimp flange - ferrule combination can be used to gain more space in the housing.
Pack contents	2 blind plates internal cable clamp with screws

Technical characteristics

Tightening torque	0.35 Nm Cable clamp screw
Ambient temperature	-55 ... +125 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP30
Cable diameter	3.3 ... 14 mm Please follow the assembly instructions!



Pushing Performance
Since 1945

Technical characteristics

Vibration resistance	Category 1B acc. to IEC 61373
Shock resistance	Category 1B acc. to IEC 61373

Material properties

Material (hood/housing)	Thermoplastic
Colour (hood/housing)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate
ECHA SCIP number	a4a9de28-6060-4c0d-b79b-5842f7db41be
California Proposition 65 substances	Not contained

Commercial data

Packaging size	10
Net weight	24.95 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140469754
eCl@ss	27440213 D-Sub hood
UNSPSC 24.0	39121416