

D-Sub plastic hood 25-pole IP67



Image is for illustration purposes only. Please refer to product description.

Part number	09 67 025 0437
Specification	D-Sub plastic hood 25-pole IP67
HARTING eCatalogue	https://harting.com/09670250437

Identification

Category	Hoods / Housings
Series	D-Sub
Identification	IP67
Type of hood/housing	Shell housing

Version

Size	D-Sub 3
Shielding	Shielded
Version	Top entry
Number of cable entries	1
Cable entry	1x
Cable fixing	Cable clamp
Locking type	Screw locking
2 parts	No
Separable	No

Technical characteristics

Tightening torque	0.4 Nm Fixing screws 0.4 Nm Cable clamp screw
Ambient temperature	-25 ... +70 °C
Degree of protection acc. to IEC 60529	IP67
Cable diameter	8 ... 10.5 mm



Pushing Performance
Since 1945

Material properties

Material (hood/housing)	Thermoplastic
Surface (hood/housing)	Metallised
Length	52 mm
Width	55.7 mm
Height	19.1 mm
RoHS	compliant with exemption
RoHS exemptions	6(a)-I: Lead as an alloying element in steel for machining purposes containing up to 0,35 % lead by weight 6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	ecef7555-f643-4ceb-a337-fc54762297f1
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Commercial data

Packaging size	10
Net weight	35.3 g
Country of origin	Czechia
European customs tariff number	85389099
GTIN	5713140091535
eCl@ss	27440213 D-Sub hood
ETIM	EC001133
UNSPSC 24.0	39121416