

D SUB MIXED FE PNEUMATIC CONTACT_4 mm



Image is for illustration purposes only. Please refer to product description.

Part number	09 69 187 0063
Specification	D SUB MIXED FE PNEUMATIC CONTACT_4 mm
HARTING eCatalogue	https://harting.com/09691870063

Identification

Category	Contacts
Series	D-Sub
Identification	Mixed
Type of contact	Pneumatic contact

Version

Gender	Female
Manufacturing process	Turned contacts

Technical characteristics

Limiting temperature	-10 ... +60 °C
Tube inner diameter	4 mm

Material properties

Material (contacts)	German silver
Material (seal)	Viton
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes

Material properties

REACH SVHC substances	Lead
ECHA SCIP number	ecef7555-f643-4ceb-a337-fc54762297f1
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Commercial data

Packaging size	20
Net weight	2.44 g
Country of origin	Czechia
European customs tariff number	85366990
GTIN	5713140097315
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522