

## D SUB MIXED MA PNEUMATIC CONTACT\_3 mm



Image is for illustration purposes only. Please refer to product description.

Part number	09 69 287 0062
Specification	D SUB MIXED MA PNEUMATIC CONTACT_3 mm
HARTING eCatalogue	<a href="https://harting.com/09692870062">https://harting.com/09692870062</a>

### Identification

Category	Contacts
Series	D-Sub
Identification	Mixed
Type of contact	Pneumatic contact

### Version

Gender	Male
Manufacturing process	Turned contacts

### Technical characteristics

Limiting temperature	-10 ... +60 °C
Tube inner diameter	3 mm

### Material properties

Material (contacts)	German silver
Material (seal)	Viton
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes

## Material properties

REACH SVHC substances	Lead
ECHA SCIP number	ecef7555-f643-4ceb-a337-fc54762297f1
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Commercial data

Packaging size	20
Net weight	1.9 g
Country of origin	Czechia
European customs tariff number	85366990
GTIN	5713140099609
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522