

Han® S 200 FC CRT 50 mm² w. rubb. sleeve



Image is for illustration purposes only. Please refer to product description.

Part number	09 93 000 6264
Specification	Han® S 200 FC CRT 50 mm ² w. rubb. sleeve
HARTING eCatalogue	https://harting.com/09930006264

Identification

Category	Contacts
Series	Han® S
Identification	Han® S 200
Type of contact	Crimp contact
Description of the contact	Female contact incl. rubber sleeve

Version

Termination method	Crimp termination
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	50 mm ²
Conductor cross-section [AWG]	AWG 1/0
Rated current	≤200 A
Contact resistance	≤0.3 mΩ
Stripping length	22 mm

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material (accessories)	Thermoplastic polyurethane (TPU)
RoHS	compliant

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

Commercial data

Packaging size	1
Net weight	47.2 g
Country of origin	China
European customs tariff number	85366990
GTIN	5713140188808
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522