

Han® S 200 FC CRT 25mm²



Image is for illustration purposes only. Please refer to product description.

Part number	09 93 000 7262
Specification	Han® S 200 FC CRT 25mm²
HARTING eCatalogue	https://harting.com/09930007262

Identification

Category	Contacts
Series	Han® S
Identification	Han® S 200
Type of contact	Crimp contact
Description of the contact	Female contact

Version

Termination method	Crimp termination
Manufacturing process	Turned contacts
Details	Using of rubber sleeve is imperative! Please order separately.

Technical characteristics

Conductor cross-section	25 mm²
Conductor cross-section [AWG]	AWG 4
Rated current	≤200 A
Contact resistance	≤0.3 mΩ
Stripping length	22 mm

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant
ELV status	compliant



Pushing Performance
Since 1945

Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

Commercial data

Packaging size	1
Net weight	40.78 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140188846
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522