

Han® S-HA (16mm)-black



Image is for illustration purposes only. Please refer to product description.

Part number	09 93 001 0501
Specification	Han® S-HA (16mm)-black
HARTING eCatalogue	https://harting.com/09930010501

Identification

Category	Hoods / Housings
Series	Han® S
Identification	Han® S 200
Type of hood/housing	Hood
Description of hood/housing	Angled

Version

Number of contacts	1
Locking type	Single locking lever
Field of application	Energy Storage Systems
Details	Please order crimp contacts separately. Please order rubber sleeve separately.

Technical characteristics

Conductor cross-section	25 ... 50 mm ²
Conductor cross-section [AWG]	AWG 4 ... AWG 1/0
Rated current	200 A
Rated voltage	1,500 V
Rated impulse voltage	8 kV
Pollution degree	2
Insulation resistance	>10 ⁸ Ω
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.



Pushing Performance
Since 1945

Technical characteristics

Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP40 mated condition IP20 unmated condition (1500 V DC; 1000 V AC)

Material properties

Material (hood/housing)	Polyamide (PA)
Colour (hood/housing)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984 UL 4128 UL 1977
Approvals	CE

Commercial data

Packaging size	1
Net weight	20.5 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140183612
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466