

## Han Hand Crimp Tool



Image is for illustration purposes only. Please refer to product description.

Part number	09 99 000 0110
Specification	Han Hand Crimp Tool
HARTING eCatalogue	<a href="https://harting.com/09990000110">https://harting.com/09990000110</a>

### Identification

Category	Tools
Type of tool	Hand crimping tool
Description of the tool	<p>Han D®: 0.14 ... 1.5 mm<sup>2</sup> (in the range from 0.14 ... 0.37 mm<sup>2</sup> only suitable for contacts 09 15 000 6104/6204 and 09 15 000 6124/6224)</p> <p>Han E®: 0.5 ... 4 mm<sup>2</sup></p> <p>Han-Yellock®: 0.5 ... 4 mm<sup>2</sup></p> <p>Han® C: 1.5 ... 4 mm<sup>2</sup></p>
Type of drive	Can be processed manually

### Version

Die set	HARTING W Crimp
Direction of movement	Parallel
Field of application	Recommended for production lines up to 10,000 crimping operations per year
Pack contents	<p>Locator Han® C</p> <p>Locator Han E®</p> <p>Locator Han D®</p> <p>Please order Han-Yellock® separately.</p>

### Technical characteristics

Conductor cross-section	0.14 ... 4 mm <sup>2</sup>
Cycles cleaning / inspection	100
Cycles crimp check	1,000
Cycles service / maintenance	10.000 (at least once a year)

## Commercial data

Packaging size	1
Net weight	735 g
Country of origin	Germany
European customs tariff number	82032000
GTIN	5713140105577
eCl@ss	21043811 Crimping pliers
ETIM	EC000168