

Battery hydraulic crimping tool 60 kN



Image is for illustration purposes only. Please refer to product description.

Identification

Category	Tools
Type of tool	Battery hydraulic tool
Description of the tool	Pressing force 60 kN Crimp die acc. to DIN 46235 with pressing width 9 mm
Type of drive	Electrical Battery

Version

Die set	Hexagonal Crimp
Direction of movement	Parallel
Field of application	Recommended for field use Recommended for stationary use in production lines
Pack contents	Lithium-Ion battery 18 V, 1.3 Ah

Termination data

Permissible voltage	220 ... 240 V
---------------------	---------------

Technical characteristics

Conductor cross-section	10 ... 70 mm ²
Cycles cleaning / inspection	100
Cycles crimp check	1,000
Cycles service / maintenance	10.000 (at least once a year)

Commercial data

Packaging size	1
Net weight	6,060 g
Country of origin	Germany
European customs tariff number	84672920
GTIN	5713140107960
ETIM	EC000168
eCl@ss	21043811 Crimping pliers