

Crimp die 25mm² for 60 kN tool



Image is for illustration purposes only. Please refer to product description.

Identification

Category	Tools
Type of tool	Crimp die
Description of the tool	for 60 kN tool

Version

Details	Identification 10 TC 70, TC 100, TC 200, TC 250, TC 350 Pressing width 9 mm
Pack contents	Supplied as a pair

Technical characteristics

Conductor cross-section	25 mm ²
Cycles cleaning / inspection	100
Cycles crimp check	1,000
Cycles service / maintenance	35.000

Specifications and approvals

Specifications	DIN 46235
----------------	-----------

Commercial data

Packaging size	1
Net weight	148.7 g
Country of origin	Germany
European customs tariff number	82073090

Commercial data

GTIN	5713140108004
eCl@ss	21043852 Insert for crimp tool
ETIM	EC001282
UNSPSC 24.0	27112820