

## Battery hydraulic crimping tool 120kN



Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Tools
Type of tool	Battery hydraulic tool
Description of the tool	Pressing force 120 kN Crimp die acc. to DIN 46235 with pressing width 10 ... 14 mm
Type of drive	Electrical Battery

### Version

Die set	Hexagonal Crimp
Direction of movement	Parallel
Field of application	Recommended for field use Recommended for stationary use in production lines
Pack contents	Lithium-Ion battery 18 V, 3 Ah

### Termination data

Permissible voltage	220 ... 240 V
---------------------	---------------

### Technical characteristics

Conductor cross-section	10 ... 240 mm <sup>2</sup>
Cycles cleaning / inspection	100
Cycles crimp check	1,000
Cycles service / maintenance	10.000 (at least once a year)

## Commercial data

Packaging size	1
Net weight	12,380 g
Country of origin	Germany
European customs tariff number	84672920
GTIN	5713140108042
ETIM	EC000168
eCl@ss	21043811 Crimping pliers