

## Hand hydraulic crimping tool 120kN



Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Tools
Type of tool	Hand hydraulic crimping tool
Description of the tool	Pressing force 120 kN Crimp die acc. to DIN 46235 with pressing width 10 ... 14 mm
Type of drive	Can be processed manually

### Version

Die set	Hexagonal Crimp
Direction of movement	Parallel

### Technical characteristics

Conductor cross-section	10 ... 240 mm <sup>2</sup>
Cycles cleaning / inspection	100
Cycles crimp check	1,000
Cycles service / maintenance	10.000 (at least once a year)

### Commercial data

Packaging size	1
Net weight	10,300 g
Country of origin	Germany
European customs tariff number	84678900
GTIN	5713140277915
ETIM	EC000168

Commercial data

eCl@ss

21043811 Crimping pliers