

## Double-Indent Pneumatic Crimping Tool



Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Tools
Type of tool	Pneumatic crimping tool
Description of the tool	<ul style="list-style-type: none"><li>Han D®: 0.14 ... 2.5 mm<sup>2</sup></li><li>Han E®: 0.14 ... 4 mm<sup>2</sup></li><li>Han® C: 1.5 ... 10 mm<sup>2</sup></li><li>D-Sub</li><li>Han® ORV3 power: 4 ... 10 mm<sup>2</sup></li></ul>
Type of drive	Pneumatic

### Version

Die set	4-mandrel two-indent crimp
Direction of movement	4 indent
Field of application	<ul style="list-style-type: none"><li>Recommended for production lines</li><li>up to 50,000 crimping operations per year</li></ul>
Pack contents	<ul style="list-style-type: none"><li>Foot switch</li><li>Locator Han D®</li><li>Locator Han E®</li><li>Locator Han® C</li><li>Pneumatic tube</li><li>Operating instructions</li></ul>

### Technical characteristics

Cycles cleaning / inspection	500
Cycles crimp check	5,000

### Technical characteristics

Cycles service / maintenance	50.000
------------------------------	--------

### Commercial data

Packaging size	1
Net weight	6.3 kg
Country of origin	Germany
European customs tariff number	84671900
GTIN	5713140301153
eCl@ss	21043811 Crimping pliers
ETIM	EC000168