

## Han-Yellock 30M-Haube-M25 straight



Image is for illustration purposes only. Please refer to product description.

Part number	11 13 300 1401
Specification	Han-Yellock 30M-Haube-M25 straight
HARTING eCatalogue	<a href="https://harting.com/11133001401">https://harting.com/11133001401</a>

### Identification

Category	Hoods / Housings
Series of hoods/housings	Han-Yellock®
Type of hood/housing	Shell

### Version

Size	Han-Yellock® 30
Version	Top entry
Number of cable entries	1
Cable entry	1x M25
Locking type	Push button
Field of application	Hoods/housings for outdoor applications

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Un-/locking temperature	-10 ... +85 °C
Degree of protection acc. to IEC 60529	IP65 IP67

### Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7021 (black grey)

## Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel Naphthalene

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
Approvals	CE DNV GL

## Commercial data

Packaging size	1
Net weight	115.75 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140110502
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466