

## Han-Yellock 60 M bulkhead housing, molly



Image is for illustration purposes only. Please refer to product description.

Part number	11 13 600 0302
Specification	Han-Yellock 60 M bulkhead housing, molly
HARTING eCatalogue	<a href="https://harting.com/11136000302">https://harting.com/11136000302</a>

### Identification

Category	Hoods / Housings
Series of hoods/housings	Han-Yellock®
Type of hood/housing	Bulkhead mounted housing

### Version

Size	Han-Yellock® 60
Field of application	Hoods/housings for outdoor applications
Pack contents	incl. 4 panel fastener

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Un-/locking temperature	-10 ... +85 °C
Degree of protection acc. to IEC 60529	IP65 IP67

### Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Passivated
Colour (hood/housing)	Metallic
Material (seal)	NBR
RoHS	compliant
ELV status	compliant

## Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
Approvals	CE DNV GL

## Commercial data

Packaging size	1
Net weight	157.7 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140110571
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466