

Han-Yellock 10 cover f. hood



Image is for illustration purposes only. Please refer to product description.

Identification

Category	Accessories
Series of hoods/housings	Han-Yellock®
Type of accessory	Protection cover
Description of the accessory	for hoods

Version

Size	Han-Yellock® 10
------	-----------------

Technical characteristics

Limiting temperature	-40 ... +125 °C
Un-/locking temperature	-10 ... +85 °C

Material properties

Material (hood/housing)	Thermoplastic
Material (seal)	NBR
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

Commercial data

Packaging size	10
Net weight	9.95 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140110700
eCl@ss	27440208 Cap for industrial connectors
ETIM	EC002314
UNSPSC 24.0	39121467