

## har-flex Board IDC 20p strain relief




Image is for illustration purposes only. Please refer to product description.

Part number	15 39 020 0603 000
Specification	har-flex Board IDC 20p strain relief
HARTING eCatalogue	<a href="https://harting.com/15390200603000">https://harting.com/15390200603000</a>

### Identification

Category	Accessories
Series	har-flex®
Identification	Board IDC
Type of accessory	Strain relief

### Version

Number of contacts	20
--------------------	----

### Technical characteristics

Limiting temperature	-55 ... +125 °C
Withdrawal force	>20 N

### Material properties

Material (accessories)	Liquid crystal polymer (LCP)
Colour (accessories)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

## Material properties

California Proposition 65 substances	Not contained
--------------------------------------	---------------

## Commercial data

Packaging size	600
Net weight	0.367 g
Country of origin	China
European customs tariff number	85366990
GTIN	5713140838062
eCl@ss	27440292 Connector component (accessories)
UNSPSC 24.0	39121400