

har-flex Board IDC 40p strain relief




Image is for illustration purposes only. Please refer to product description.

Part number	15 39 040 0603 000
Specification	har-flex Board IDC 40p strain relief
HARTING eCatalogue	https://harting.com/15390400603000

Identification

Category	Accessories
Series	har-flex®
Identification	Board IDC
Type of accessory	Strain relief

Version

Number of contacts	40
--------------------	----

Technical characteristics

Limiting temperature	-55 ... +125 °C
Withdrawal force	>20 N

Material properties

Material (accessories)	Liquid crystal polymer (LCP)
Colour (accessories)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained



Pushing Performance
Since 1945

Material properties

California Proposition 65 substances Not contained

Commercial data

Packaging size	600
Net weight	0.55 g
Country of origin	China
European customs tariff number	85366990
GTIN	5713140837645
eCl@ss	27440292 Connector component (accessories)
UNSPSC 24.0	39121400