

Spec. Cable Gland M25 Cable-Ø17-22.5

	Part number	19 00 000 5025
	Specification	Spec. Cable Gland M25 Cable-Ø17-22.5
	HARTING eCatalogue	https://b2b.harting.com/19000005025

Identification

Category	Accessories
Series of hoods/housings	Han® HPR EasyCon
Type of accessory	Cable gland
Description of the accessory	EMC version

Technical characteristics

Tightening torque	20 Nm
Wrench size	32
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP65 / IP68
Size	M25
Clamping range	17 ... 22.5 mm
Width across corners	33 mm 33.4 mm

Material properties

Material (seal)	EPDM
Material (cable glands)	Brass
Material (clamping ring)	Polyamide (PA)
Surface (accessories)	Nickel plated

Commercial data

Packaging size	1
Net weight	84 g

Commercial data

Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27144432 Screwed cable gland (electr.)