

Spec. Cable Gland M40/13mm Ø16-28 SBC



Image is for illustration purposes only. Please refer to product description.

Identification

Category	Accessories
Series of hoods/housings	Han® HPR EasyCon
Type of accessory	Cable gland
Description of the accessory	EMC version

Technical characteristics

Tightening torque	30 Nm
Wrench size	44
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP65 / IP68
Size	M40
Clamping range	16 ... 28 mm
Width across corners	47 mm

Material properties

Material (cable glands)	Brass
Material (seal)	EPDM
Material (clamping ring)	Polyamide (PA)
Surface (accessories)	Nickel plated

Commercial data

Packaging size	1
Net weight	298 g

Commercial data

Country of origin	Germany
European customs tariff number	74122000
GTIN	5713140193208
eCl@ss	27140803 Cable gland EMC (electrical installation)
ETIM	EC000441
UNSPSC 24.0	39121431