

## Spec. Cable Gland M40/12mm Ø21-35 SBC



Image is for illustration purposes only. Please refer to product description.

Part number	19 00 000 5032
Specification	Spec. Cable Gland M40/12mm Ø21-35 SBC
HARTING eCatalogue	<a href="https://harting.com/19000005032">https://harting.com/19000005032</a>

### Identification

Category	Accessories
Series of hoods/housings	Han® HPR EasyCon
Type of accessory	Cable gland
Description of the accessory	EMC version

### Technical characteristics

Tightening torque	30 Nm
Wrench size	51
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP65 / IP68
Size	M40
Clamping range	21 ... 35 mm
Width across corners	54 mm

### Material properties

Material (cable glands)	Brass
Material (seal)	EPDM
Material (clamping ring)	Polyamide (PA)
Surface (accessories)	Nickel plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50

## Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Commercial data

Packaging size	1
Net weight	335 g
Country of origin	Germany
European customs tariff number	74122000
GTIN	5713140193215
eCl@ss	27140803 Cable gland EMC (electrical installation)
ETIM	EC000441
UNSPSC 24.0	39121431