

Spec. Cable Gland M50/30mm Ø21-35 SBC



Image is for illustration purposes only. Please refer to product description.

Part number	19 00 000 5034
Specification	Spec. Cable Gland M50/30mm Ø21-35 SBC
HARTING eCatalogue	https://harting.com/19000005034

Identification

Category	Accessories
Series of hoods/housings	Han® HPR EasyCon
Type of accessory	Cable gland
Description of the accessory	EMC version

Technical characteristics

Tightening torque	30 Nm
Wrench size	51 53
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP65 / IP68
Size	M50
Clamping range	21 ... 35 mm
Width across corners	54 mm 56 mm

Material properties

Material (cable glands)	Brass
Material (seal)	EPDM
Material (clamping ring)	Polyamide (PA)
Surface (accessories)	Nickel plated

Commercial data

Packaging size	1
----------------	---

Commercial data

Net weight	349 g
Country of origin	Germany
European customs tariff number	74122000
GTIN	5713140193222
eCl@ss	27140803 Cable gland EMC (electrical installation)
ETIM	EC000441
UNSPSC 24.0	39121431