

Han CGM-M M25x1,5 D.13-18mm



Image is for illustration purposes only. Please refer to product description.

Part number	19 00 000 5092
Specification	Han CGM-M M25x1,5 D.13-18mm
HARTING eCatalogue	https://harting.com/19000005092

Identification

Category	Accessories
Series of hoods/housings	Han® CGM-M
Type of accessory	Cable gland

Technical characteristics

Tightening torque	≤12 Nm (depending on the cable and the seal insert used)
Wrench size	30
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP68 IP69 / IPX9K acc. to ISO 20653
Size	M25
Clamping range	13 ... 18 mm
Width across corners	33.5 mm

Material properties

Material (cable glands)	Brass
Material (seal)	NBR
Material (clamping ring)	Polyamide (PA)
Surface (accessories)	Nickel plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50

Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	6fb545c1-f438-46c2-b07a-8552e7e5a3d7
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

UL / CSA	UL 514B QCRV.E479780 CSA-C22.2 No. 18.3 QCRV7.E479780
Approvals	DNV GL

Commercial data

Packaging size	10
Net weight	50.87 g
Country of origin	Germany
European customs tariff number	74122000
GTIN	5713140123793
eCl@ss	27140801 Screwed cable gland (electrical)
ETIM	EC000441
UNSPSC 24.0	39121431