

## CABLE CLAMP M20, 6-12m, THERMOPLASTIC BL



Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Accessories
Type of accessory	Cable gland

### Technical characteristics

Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP68
Size	M20
Clamping range	6 ... 12 mm

### Material properties

Material (cable glands)	Thermoplastic
Colour (cable gland)	Black
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

### Commercial data

Packaging size	10
Net weight	10.92 g

### Commercial data

Country of origin	Germany
European customs tariff number	39174000
GTIN	5713140123861
eCl@ss	27140801 Screwed cable gland (electrical)
ETIM	EC000441
UNSPSC 24.0	39121431