

Han CGM M50 17-28 mm - short



Image is for illustration purposes only. Please refer to product description.

Identification

Category	Accessories
Series of hoods/housings	Han® CGM-M
Type of accessory	Cable gland
Description of the accessory	Railway version Short version

Technical characteristics

Tightening torque	16 Nm
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP65 IP67
Size	M50
Clamping range	17 ... 28 mm
Width across corners	55 mm

Material properties

Material (cable glands)	Brass
Material (seal)	EPDM
Surface (accessories)	Nickel plated
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained

Material properties

REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	163.1 g
Country of origin	Germany
European customs tariff number	74122000
GTIN	5713140537422
eCl@ss	27140801 Screwed cable gland (electrical)
UNSPSC 24.0	39121431