

## Han CGM-P-EXi M25 D 9...16mm



Image is for illustration purposes only. Please refer to product description.

Part number	19 00 000 7104
Specification	Han CGM-P-EXi M25 D 9...16mm
HARTING eCatalogue	<a href="https://harting.com/19000007104">https://harting.com/19000007104</a>

### Identification

Category	Accessories
Series of hoods/housings	Han <sup>®</sup> CGM-Ex i
Type of accessory	Cable gland

### Version

Field of application	Intrinsically safe electric circuits
----------------------	--------------------------------------

### Technical characteristics

Tightening torque	≤5 Nm (depending on the cable and the seal insert used)
Wrench size	33
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP68 IP69 / IPX9K acc. to ISO 20653
Size	M25
Clamping range	9 ... 16 mm
Width across corners	33.5 mm

### Material properties

Material (cable glands)	Polyamide (PA)
Colour (cable gland)	RAL 5012 (light blue) RAL 9005 (jet black)
Material (seal)	NBR
Material flammability class acc. to UL 94	V-0
RoHS	compliant



**Pushing Performance**  
Since 1945

## Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	1
Net weight	23.38 g
Country of origin	Germany
European customs tariff number	39174000
GTIN	5713140192850
eCl@ss	27140802 Screwed cable gland (explosion-proof, electrical)
ETIM	EC000441
UNSPSC 24.0	39121431