

Han CGM-M-Rail M32 D.20.5-25mm



Image is for illustration purposes only. Please refer to product description.

Part number	19 00 000 7125
Specification	Han CGM-M-Rail M32 D.20.5-25mm
HARTING eCatalogue	https://harting.com/19000007125

Identification

Category	Accessories
Series of hoods/housings	Han® CGM-M-Rail
Type of accessory	Cable gland
Description of the accessory	Railway version

Technical characteristics

Tightening torque	≤8 Nm (depending on the cable and the seal insert used)
Wrench size	36
	40
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP68
Size	M32
Clamping range	20.5 ... 25 mm
Width across corners	43.9 mm

Material properties

Material (cable glands)	Brass
Material (seal)	EPDM
Surface (accessories)	Nickel plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50



Pushing Performance
Since 1945

Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	10
Net weight	121.3 g
Country of origin	Germany
European customs tariff number	74122000
GTIN	5713140193154
eCl@ss	27140801 Screwed cable gland (electrical)
ETIM	EC000441
UNSPSC 24.0	39121431