

Cable Seal M25x1,5 Metal 14-17mm



Image is for illustration purposes only. Please refer to product description.

Part number	19 12 000 5058
Specification	Cable Seal M25x1,5 Metal 14-17mm
HARTING eCatalogue	https://harting.com/19120005058

Identification

Category	Accessories
Series of hoods/housings	Han-Compact®
Type of accessory	Cable gland
Description of the accessory	for hoods

Technical characteristics

Tightening torque	≤10 Nm (depending on the cable and the seal insert used)
Wrench size	28
Limiting temperature	-40 ... +130 °C
Degree of protection acc. to IEC 60529	IP65
Size	M25
Clamping range	14 ... 17 mm

Material properties

Material (cable glands)	Metal
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes

Material properties

REACH SVHC substances	Lead 2-(2'-Hydroxy-3'-tert-butyl-5'-methylphenyl)-5-chlorobenzotriazole (UV-326)
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Commercial data

Packaging size	10
Net weight	0.01 g
Country of origin	Germany
European customs tariff number	74122000
GTIN	5713140124028
eCl@ss	27140807 Additional components cable gland
ETIM	EC003608
UNSPSC 24.0	39121431