

## Cable Seal plastic M25x1.5 10.5-14mm



Image is for illustration purposes only. Please refer to product description.

Part number	19 12 000 5157
Specification	Cable Seal plastic M25x1.5 10.5-14mm
HARTING eCatalogue	<a href="https://harting.com/19120005157">https://harting.com/19120005157</a>

### Identification

Category	Accessories
Series of hoods/housings	Han-Compact®
Type of accessory	Cable gland
Description of the accessory	for hoods for cable to cable housing

### Technical characteristics

Tightening torque	≤6 Nm (depending on the cable and the seal insert used)
Wrench size	30
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP65
Size	M25
Clamping range	10.5 ... 14 mm

### Material properties

Material (cable glands)	Thermoplastic
Colour (cable gland)	Black
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes

## Material properties

REACH SVHC substances	2-(2'-Hydroxy-3'-tert-butyl-5'-methylphenyl)-5-chlorobenzotriazole (UV-326)
California Proposition 65 substances	Not contained

## Commercial data

Packaging size	10
Net weight	7 g
Country of origin	Germany
European customs tariff number	39174000
GTIN	5713140124066
eCl@ss	27140807 Additional components cable gland
ETIM	EC003608
UNSPSC 24.0	39121431