

## Han-Compact-HTE-M25-black



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 19 12 008 0411                                                                |
| Specification      | Han-Compact-HTE-M25-black                                                     |
| HARTING eCatalogue | <a href="https://harting.com/19120080411">https://harting.com/19120080411</a> |

### Identification

|                             |                                                                                                                 |
|-----------------------------|-----------------------------------------------------------------------------------------------------------------|
| Category                    | Hoods / Housings                                                                                                |
| Series of hoods/housings    | Han-Compact®                                                                                                    |
| Type of hood/housing        | Hood                                                                                                            |
| Description of hood/housing | for Han-Compact® half cable gland<br>With separate PE terminating point<br>for all inserts of size Han-Compact® |

### Version

|                         |                                            |
|-------------------------|--------------------------------------------|
| Size                    | Han-Compact®                               |
| Version                 | Top entry                                  |
| Number of cable entries | 1                                          |
| Cable entry             | 1x M25                                     |
| Locking type            | Single locking lever                       |
| Field of application    | Hoods/housings for industrial applications |

### Technical characteristics

|                                        |                                                |
|----------------------------------------|------------------------------------------------|
| Limiting temperature                   | -40 ... +125 °C                                |
| Note on the limiting temperature       | For use as a connector according to IEC 61984. |
| Degree of protection acc. to IEC 60529 | IP65                                           |
| Type rating acc. to UL 50 / UL 50E     | 12                                             |

### Material properties

|                         |               |
|-------------------------|---------------|
| Material (hood/housing) | Zinc die-cast |
|-------------------------|---------------|



**Pushing Performance**  
Since 1945

## Material properties

|                                      |                      |
|--------------------------------------|----------------------|
| Surface (hood/housing)               | Chromated            |
| Colour (hood/housing)                | RAL 9005 (jet black) |
| RoHS                                 | not compliant        |
| ELV status                           | not compliant        |
| REACH Annex XVII substances          | Not contained        |
| REACH ANNEX XIV substances           | Not contained        |
| REACH SVHC substances                | Not contained        |
| California Proposition 65 substances | Yes                  |
| California Proposition 65 substances | Lead<br>Nickel       |

## Specifications and approvals

|           |                                   |
|-----------|-----------------------------------|
| UL / CSA  | UL 1977 ECBT2.E235076             |
|           | UL 2237 PVVA2.E318390             |
|           | CSA-C22.2 No. 182.3 ECBT8.E235076 |
|           | CSA-C22.2 No. 182.3 PVVA8.E318390 |
| Approvals | CE<br>DNV GL                      |

## Commercial data

|                                |                                          |
|--------------------------------|------------------------------------------|
| Packaging size                 | 1                                        |
| Net weight                     | 200 g                                    |
| Country of origin              | Romania                                  |
| European customs tariff number | 85389099                                 |
| GTIN                           | 5713140124080                            |
| eCl@ss                         | 27440202 Shell for industrial connectors |
| ETIM                           | EC000437                                 |
| UNSPSC 24.0                    | 39121466                                 |