

## Han Compact-gs-M25-SW-Metal



Image is for illustration purposes only. Please refer to product description.

Part number	19 12 708 0511
Specification	Han Compact-gs-M25-SW-Metal
HARTING eCatalogue	<a href="https://harting.com/19127080511">https://harting.com/19127080511</a>

### Identification

Category	Hoods / Housings
Series of hoods/housings	Han-Compact®
Type of hood/housing	Hood
Description of hood/housing	for Han-Compact® half cable gland With separate PE terminating point for all inserts of size Han-Compact®

### Version

Size	Han-Compact®
Version	Side entry
Number of cable entries	1
Cable entry	1x M25
Locking type	Single locking lever
Field of application	Hoods/housings for industrial applications

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	12

### Material properties

Material (hood/housing)	Zinc die-cast
-------------------------	---------------

## Material properties

Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 UL 2237 PVVA2.E318390 CSA-C22.2 No. 182.3 ECBT8.E235076 CSA-C22.2 No. 182.3 PVVA8.E318390
Approvals	CE DNV GL

## Commercial data

Packaging size	1
Net weight	193.5 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140124233
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466