

Han CGM-P F+B M25x1,5 D. 11-13 black



Image is for illustration purposes only. Please refer to product description.

Part number	19 15 503 5196
Specification	Han CGM-P F+B M25x1,5 D. 11-13 black
HARTING eCatalogue	https://harting.com/19155035196

Identification

Category	Accessories
Series of hoods/housings	Han® F+B
Type of accessory	Cable gland

Version

Pack contents	With spacing washer
---------------	---------------------

Technical characteristics

Wrench size	32
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP67 / IP69
Size	M25
Clamping range	11 ... 13 mm

Material properties

Roughness of the surface	≤0.8 µm
Material (cable glands)	Polyamide (PA)
Colour (cable gland)	Black
Colour (seal)	Blue
Material (accessories)	VA 1.4305
RoHS	compliant
ELV status	compliant
China RoHS	e

Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Approvals	Ecolab Topactive 200 Ecolab Topactive 500 Ecolab Topax 66 Ecolab Topactive OKTO Ecolab Topax 990 FDA 21 CFR 177.1500 FDA 21 CFR 176.170 (c) FDA 21 CFR 177.1390 FDA 21 CFR 177.1395 FDA 21 CFR 177.2600
-----------	--

Commercial data

Packaging size	1
Net weight	31 g
Country of origin	Germany
European customs tariff number	84849000
GTIN	5713140192751
eCl@ss	27140801 Screwed cable gland (electrical)
ETIM	EC000441
UNSPSC 24.0	39121431