

Han CGM-P F+B M25x1,5 D. 16-18 black



Image is for illustration purposes only. Please refer to product description.

Identification

Category	Accessories
Series of hoods/housings	Han® F+B
Type of accessory	Cable gland

Version

Pack contents	With spacing washer
---------------	---------------------

Technical characteristics

Wrench size	32
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP67 / IP69
Size	M25
Clamping range	16 ... 18 mm

Material properties

Roughness of the surface	≤0.8 µm
Material (cable glands)	Polyamide (PA)
Colour (cable gland)	Black
Colour (seal)	Blue
Material (accessories)	VA 1.4305
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption

Material properties

China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

Approvals	Ecolab Topactive 200 Ecolab Topactive 500 Ecolab Topax 66 Ecolab Topactive OKTO Ecolab Topax 990 FDA 21 CFR 177.1500 FDA 21 CFR 176.170 (c) FDA 21 CFR 177.1390 FDA 21 CFR 177.1395 FDA 21 CFR 177.2600
-----------	--

Commercial data

Packaging size	1
Net weight	30 g
Country of origin	Germany
European customs tariff number	39174000
GTIN	5713140192775
eCl@ss	27140801 Screwed cable gland (electrical)
ETIM	EC000441
UNSPSC 24.0	39121431