

## Han CGM-P F+B M25X1,5 D. 11-13 nature



Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Accessories
Series of hoods/housings	Han® F+B
Type of accessory	Cable gland

### Version

Pack contents	With spacing washer
---------------	---------------------

### Technical characteristics

Wrench size	32
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP67 / IP69
Size	M25
Clamping range	11 ... 13 mm

### Material properties

Roughness of the surface	≤0.8 µm
Material (cable glands)	Polyamide (PA)
Colour (cable gland)	White
Colour (seal)	Blue
Material (accessories)	VA 1.4305

## Specifications and approvals

Approvals	Ecolab Topactive 200 Ecolab Topactive 500 Ecolab Topax 66 Ecolab Topactive OKTO Ecolab Topax 990 FDA 21 CFR 177.1500 FDA 21 CFR 176.170 (c) FDA 21 CFR 177.1390 FDA 21 CFR 177.1395 FDA 21 CFR 177.2600
-----------	--

## Commercial data

Packaging size	1
Net weight	31.5 g
Country of origin	Germany
European customs tariff number	84849000
GTIN	5713140192799
eCl@ss	27140801 Screwed cable gland (electrical)
ETIM	EC000441
UNSPSC 24.0	39121431