

HAN CGM-P F+B M25X1,5 D. 13-16 nature



Image is for illustration purposes only. Please refer to product description.

Part number	19 15 523 5197
Specification	HAN CGM-P F+B M25X1,5 D. 13-16 nature
HARTING eCatalogue	https://harting.com/19155235197

Identification

Category	Accessories
Series of hoods/housings	Han® F+B
Type of accessory	Cable gland

Version

Pack contents	With spacing washer
---------------	---------------------

Technical characteristics

Wrench size	32
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP67 / IP69
Size	M25
Clamping range	13 ... 16 mm

Material properties

Roughness of the surface	≤0.8 µm
Material (cable glands)	Polyamide (PA)
Colour (cable gland)	White
Colour (seal)	Blue
Material (accessories)	VA 1.4305
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption



Pushing Performance
 Since 1945

Material properties

China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

Approvals	Ecolab Topactive 200
	Ecolab Topactive 500
	Ecolab Topax 66
	Ecolab Topactive OKTO
	Ecolab Topax 990
	FDA 21 CFR 177.1500
	FDA 21 CFR 176.170 (c)
	FDA 21 CFR 177.1390
	FDA 21 CFR 177.1395
	FDA 21 CFR 177.2600

Commercial data

Packaging size	1
Net weight	32.66 g
Country of origin	Germany
European customs tariff number	84849000
GTIN	5713140192805
eCl@ss	27140801 Screwed cable gland (electrical)
ETIM	EC000441
UNSPSC 24.0	39121431