

## Han 3A-HSM angled-L-M20 bottom closed



Image is for illustration purposes only. Please refer to product description.

Part number	19 20 003 1259
Specification	Han 3A-HSM angled-L-M20 bottom closed
HARTING eCatalogue	<a href="https://harting.com/19200031259">https://harting.com/19200031259</a>

### Identification

Category	Hoods / Housings
Series of hoods/housings	Han A®
Type of hood/housing	Surface mounted housing
Description of hood/housing	Bottom closed Fixing hole for M4 screw

### Version

Size	3 A
Version	Top entry
Number of cable entries	1
Cable entry	1x M20
Locking type	Single locking lever
Field of application	Standard Hoods/housings for industrial applications
Pack contents	Please order seal screw separately.

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP44 IP65 With seal screw IP67 With seal screw
Type rating acc. to UL 50 / UL 50E	12

## Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (locking)	Steel
Surface (locking)	Zinc plated

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
Approvals	CE DNV GL

## Commercial data

Packaging size	10
Net weight	78 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140284319
eCl@ss	27440202 Shell for industrial connectors
UNSPSC 24.0	39121466