

Han 3A hood HMC TE M20 glued seal



Image is for illustration purposes only. Please refer to product description.

Part number	19 20 203 1443
Specification	Han 3A hood HMC TE M20 glued seal
HARTING eCatalogue	https://harting.com/19202031443

Identification

Category	Hoods / Housings
Series of hoods/housings	Han® HMC
Type of hood/housing	Hood
Description of hood/housing	for Han-Brid® With glued seal

Version

Size	3 A
Version	Top entry
Number of cable entries	1
Cable entry	1x M20
Locking type	Single locking lever
Field of application	Special hoods and housings for high mating cycles
Details	Han® 3 A HMC housings shall only be combined with housings from the Han® 3 A HMC portfolio.

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Mating cycles	≥10,000
Note on the mating cycles	Mating cycles with other HMC components
Degree of protection acc. to IEC 60529	IP44 IP65 / IP67 with seal screw 09 20 000 9918

Technical characteristics

Type rating acc. to UL 50 / UL 50E	12
------------------------------------	----

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR
Material (locking)	Steel
Surface (locking)	Zinc plated

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	10
Net weight	64.6 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140170711
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466