

## Han 10B HTE M25 PFT CL



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 19 30 010 1141                                                                |
| Specification      | Han 10B HTE M25 PFT CL                                                        |
| HARTING eCatalogue | <a href="https://harting.com/19300101141">https://harting.com/19300101141</a> |

### Identification

|                          |                            |
|--------------------------|----------------------------|
| Category                 | Hoods / Housings           |
| Series of hoods/housings | Han <sup>®</sup> B         |
| Type of hood/housing     | Panel feed through housing |
| Type                     | High construction          |

### Version

|                         |                                                   |
|-------------------------|---------------------------------------------------|
| Size                    | 10 B                                              |
| Version                 | Top entry                                         |
| Number of cable entries | 1                                                 |
| Cable entry             | 1x M25                                            |
| Locking type            | Central locking lever (on the hood)               |
| Field of application    | Standard hoods/housings for industrial connectors |

### Technical characteristics

|                                        |                                                |
|----------------------------------------|------------------------------------------------|
| Limiting temperature                   | -40 ... +125 °C                                |
| Note on the limiting temperature       | For use as a connector according to IEC 61984. |
| Mating cycles                          | ≥500                                           |
| Degree of protection acc. to IEC 60529 | IP65                                           |

### Material properties

|                         |                      |
|-------------------------|----------------------|
| Material (hood/housing) | Aluminium die-cast   |
| Surface (hood/housing)  | Powder-coated        |
| Colour (hood/housing)   | RAL 7037 (dust grey) |



**Pushing Performance**  
Since 1945

## Material properties

|                                     |                            |
|-------------------------------------|----------------------------|
| Material (seal)                     | NBR                        |
| RoHS                                | compliant                  |
| ELV status                          | compliant                  |
| China RoHS                          | e                          |
| REACH Annex XVII substances         | Not contained              |
| REACH ANNEX XIV substances          | Not contained              |
| REACH SVHC substances               | Not contained              |
| Fire protection on railway vehicles | EN 45545-2 (2020-08)       |
| Requirement set with Hazard Levels  | R1 (HL 1-3)<br>R7 (HL 1-3) |

## Specifications and approvals

|           |                                                            |
|-----------|------------------------------------------------------------|
| UL / CSA  | UL 1977 ECBT2.E235076<br>CSA-C22.2 No. 182.3 ECBT8.E235076 |
| Approvals | CE<br>DNV GL                                               |

## Commercial data

|                                |                                          |
|--------------------------------|------------------------------------------|
| Packaging size                 | 1                                        |
| Net weight                     | 293.84 g                                 |
| Country of origin              | China                                    |
| European customs tariff number | 85389099                                 |
| GTIN                           | 5713140164680                            |
| eCl@ss                         | 27440202 Shell for industrial connectors |
| ETIM                           | EC000437                                 |
| UNSPSC 24.0                    | 39121466                                 |