

## Han 3M-Base angled-M25



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 19 37 003 1165                                                                |
| Specification      | Han 3M-Base angled-M25                                                        |
| HARTING eCatalogue | <a href="https://harting.com/19370031165">https://harting.com/19370031165</a> |

### Identification

|                             |                       |
|-----------------------------|-----------------------|
| Category                    | Hoods / Housings      |
| Series of hoods/housings    | Han <sup>®</sup> M    |
| Type of hood/housing        | Screw mounted housing |
| Description of hood/housing | Angled                |

### Version

|                         |                                       |
|-------------------------|---------------------------------------|
| Size                    | 3 A                                   |
| Number of cable entries | 1                                     |
| Cable entry             | 1x M25                                |
| Locking type            | Single locking lever                  |
| Field of application    | Hoods/housings for rough environments |
| Pack contents           | With seal screw                       |

### Technical characteristics

|                                        |                                                      |
|----------------------------------------|------------------------------------------------------|
| Limiting temperature                   | -40 ... +125 °C                                      |
| Note on the limiting temperature       | For use as a connector according to IEC 61984.       |
| Degree of protection acc. to IEC 60529 | IP44<br>IP65 With seal screw<br>IP67 With seal screw |

### Material properties

|                         |                      |
|-------------------------|----------------------|
| Material (hood/housing) | Zinc die-cast        |
| Surface (hood/housing)  | Powder-coated        |
| Colour (hood/housing)   | RAL 9005 (jet black) |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |                                                        |
|--------------------------------------|--------------------------------------------------------|
| Material (locking)                   | Stainless steel                                        |
| RoHS                                 | compliant with exemption                               |
| RoHS exemptions                      | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status                           | compliant with exemption                               |
| China RoHS                           | 50                                                     |
| REACH Annex XVII substances          | Not contained                                          |
| REACH ANNEX XIV substances           | Not contained                                          |
| REACH SVHC substances                | Yes                                                    |
| REACH SVHC substances                | Lead                                                   |
| California Proposition 65 substances | Yes                                                    |
| California Proposition 65 substances | Lead<br>Nickel                                         |
| Fire protection on railway vehicles  | EN 45545-2 (2020-08) + A1 (2023-10)                    |
| Requirement set with Hazard Levels   | R1 (HL 1-3)<br>R7 (HL 1-3)                             |

## Specifications and approvals

|           |              |
|-----------|--------------|
| Approvals | CE<br>DNV GL |
|-----------|--------------|

## Commercial data

|                                |                                          |
|--------------------------------|------------------------------------------|
| Packaging size                 | 10                                       |
| Net weight                     | 104.1 g                                  |
| Country of origin              | Germany                                  |
| European customs tariff number | 85389099                                 |
| GTIN                           | 5713140170971                            |
| eCl@ss                         | 27440202 Shell for industrial connectors |
| ETIM                           | EC000437                                 |
| UNSPSC 24.0                    | 39121466                                 |