

Han 24HPR EasyCon cover 3xM25-M32-M10



Image is for illustration purposes only. Please refer to product description.

Part number	19 40 024 9934
Specification	Han 24HPR EasyCon cover 3xM25-M32-M10
HARTING eCatalogue	https://harting.com/19400249934

Identification

Category	Hoods / Housings
Series of hoods/housings	Han [®] HPR EasyCon
Type of hood/housing	Mounting cover
Description of hood/housing	for surface mounted housings for hoods

Version

Size	24 B
Number of cable entries	5
Cable entry	1x M10 3x M25 1x M32
Locking type	Screw locking
Field of application	Hoods/housings for harsh outdoor environments

Technical characteristics

Tightening torque	6 Nm Mounting cover 6 Nm Distance bolt 6 Nm Fixing screws
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65 IP68 IP69 / IPX9K acc. to ISO 20653



Pushing Performance
 Since 1945

Technical characteristics

Type rating acc. to UL 50 / UL 50E	4
	4X
	12

Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	217.75 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140830776
eCl@ss	27440208 Cap for industrial connectors
ETIM	EC002314
UNSPSC 24.0	39121467