

## Han 48HPR mounting cover 1xM63



Part number	19 40 048 9824
Specification	Han 48HPR mounting cover 1xM63
HARTING eCatalogue	<a href="https://harting.com/19400489824">https://harting.com/19400489824</a>

Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Hoods / Housings
Series of hoods/housings	Han® HPR
Type of hood/housing	Mounting cover
Description of hood/housing	Distance bolt M6

### Version

Size	48 B
Number of cable entries	1
Cable entry	1x M63
Locking type	Screw locking
Field of application	Hoods/housings for harsh outdoor environments
	4 distance pieces
Pack contents	4x M6 screw
	4 washers

### Technical characteristics

Tightening torque (screw locking)	4 Nm
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
	IP65
Degree of protection acc. to IEC 60529	IP68
	IP69 / IPX9K acc. to ISO 20653

## Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
Material (locking)	Stainless steel

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	1
Net weight	640.64 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140173569
eCl@ss	27440208 Cap for industrial connectors
ETIM	EC002314
UNSPSC 24.0	39121467