

Han-Eco Cable gland M25



Image is for illustration purposes only. Please refer to product description.

Part number	19 41 000 5121
Specification	Han-Eco Cable gland M25
HARTING eCatalogue	https://harting.com/19410005121

Identification

Category	Accessories
Series of hoods/housings	Han-Eco®
Type of accessory	Cable gland

Technical characteristics

Tightening torque	10 Nm Fitting 4 Nm Cap nut
Wrench size	29
Limiting temperature	-40 ... +125 °C
Size	M25
Clamping range	9 ... 17 mm

Material properties

Material (cable glands)	Polyamide (PA)
Colour (cable gland)	RAL 9005 (jet black)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)



Pushing Performance
Since 1945

Material properties

Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)

Commercial data

Packaging size	2
Net weight	16 g
Country of origin	Germany
European customs tariff number	39174000
GTIN	5713140193000
eCl@ss	27140801 Screwed cable gland (electrical)
ETIM	EC000441
UNSPSC 24.0	39121431