

## Han-Eco 10B-HBM/RA-for DL-with cover



Image is for illustration purposes only. Please refer to product description.

Part number	19 43 010 0312
Specification	Han-Eco 10B-HBM/RA-for DL-with cover
HARTING eCatalogue	<a href="https://harting.com/19430100312">https://harting.com/19430100312</a>

### Identification

Category	Hoods / Housings
Series of hoods/housings	Han-Eco® B
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	With thermo-plastic cover Without frame

### Version

Size	10 B
Locking type	Double locking lever (on the hood)
Details	Please order frame 19 43 010 0001 separately.

### Technical characteristics

Tightening torque	1 Nm Fixing screws M4
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP66

### Material properties

Material (hood/housing)	Polyamide (PA) Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
Colour (seal)	RAL 9005 (jet black)

## Material properties

Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-2) R23 (HL 1-3)

## Specifications and approvals

Specifications	IEC 61984 EN 45545-2 Fire protection on railway vehicles
Approvals	CE

## Commercial data

Packaging size	1
Net weight	78.75 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140177970
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466