

## Han-Eco 16B-HBM-with SL-with cover



Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 19 43 016 0341  |
| Specification      | Han-Eco 16B-HBM-with SL-with cover  |
| HARTING eCatalogue | <a href="https://harting.com/19430160341">https://harting.com/19430160341</a> |

### Identification

|                             |                           |
|-----------------------------|---------------------------|
| Category                    | Hoods / Housings          |
| Series of hoods/housings    | Han-Eco® B                |
| Type of hood/housing        | Bulkhead mounted housing  |
| Description of hood/housing | With thermo-plastic cover |

### Version

|              |                      |
|--------------|----------------------|
| Size         | 16 B                 |
| Locking type | Single locking lever |

### Technical characteristics

|  |  |
|--|--|
| Tightening torque                      | 1 Nm Fixing screws M4                          |
| Limiting temperature                   | -40 ... +125 °C                                |
| Note on the limiting temperature       | For use as a connector according to IEC 61984. |
| Number of relockings                   | ≥500   |
| Degree of protection acc. to IEC 60529 | IP66   |

### Material properties

|                         |  |
|-------------------------|--|
| Material (hood/housing) | Polyamide (PA)<br>Fibre-glass reinforced |
| Colour (hood/housing)   | RAL 9005 (jet black)                     |
| Material (seal)         | NBR                                      |
| Colour (seal)           | RAL 9005 (jet black)                     |
| Material (locking)      | Polyamide (PA)<br>Fibre-glass reinforced |



Pushing Performance  
Since 1945

## Material properties

|  |                                     |
|--|-------------------------------------|
| Colour (locking)   | RAL 9005 (jet black)                |
| Material flammability class acc. to UL 94                  | V-0                                 |
| Material flammability class acc. to UL 94 (locking levers) | V-0                                 |
| RoHS   | compliant                           |
| ELV status   | compliant                           |
| China RoHS   | e                                   |
| REACH Annex XVII substances                                | Not contained                       |
| REACH ANNEX XIV substances                                 | Not contained                       |
| REACH SVHC substances                                      | Not contained                       |
| California Proposition 65 substances                       | Not contained                       |
| Fire protection on railway vehicles                        | EN 45545-2 (2020-08) + A1 (2023-10) |
| Requirement set with Hazard Levels                         | R22 (HL 1-2)<br>R23 (HL 1-3)        |

## Specifications and approvals

|                |   |
|----------------|---|
| Specifications | IEC 61984<br>EN 45545-2 Fire protection on railway vehicles |
| Approvals      | CE  |

## Commercial data

|                                |  |
|--------------------------------|--|
| Packaging size                 | 1  |
| Net weight                     | 160.52 g                                 |
| Country of origin              | Germany                                  |
| European customs tariff number | 85389099                                 |
| GTIN                           | 5713140179585                            |
| eCl@ss                         | 27440202 Shell for industrial connectors |
| ETIM                           | EC000437                                 |
| UNSPSC 24.0                    | 39121466                                 |