

Cable Gland M20 6-13 mm Stainless Steel



Image is for illustration purposes only. Please refer to product description.

Part number	19 44 000 5082
Specification	Cable Gland M20 6-13 mm Stainless Steel
HARTING eCatalogue	https://harting.com/19440005082

Identification

Category	Accessories
Series of hoods/housings	Han-INOX®
Type of accessory	Cable gland

Technical characteristics

Degree of protection acc. to IEC 60529	IP68 IP69 / IPX9K acc. to ISO 20653
Size	M20
Clamping range	6 ... 13 mm

Material properties

Material (cable glands)	Stainless steel
Material (clamping ring)	Polyamide (PA)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

Commercial data

Packaging size	10
Net weight	30 g
Country of origin	Germany
European customs tariff number	73072910
GTIN	5713140131903
eCl@ss	27140801 Screwed cable gland (electrical)
ETIM	EC000441
UNSPSC 24.0	39121431