

Han-INOX 3A-HBM-DL-C



Image is for illustration purposes only. Please refer to product description.

Part number	19 44 003 0305
Specification	Han-INOX 3A-HBM-DL-C
HARTING eCatalogue	https://harting.com/19440030305

Identification

Category	Hoods / Housings
Series of hoods/housings	Han-INOX®
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	Straight With metal cover

Version

Size	3 A
Locking type	Single locking lever
Field of application	Hoods/housings for harsh environments
Details	for mounted male insert IP rating in locked position, see technical characteristics degree of protection acc. to IEC 60529
Pack contents	With seal screw

Technical characteristics

Tightening torque	1 Nm Fixing screws M3
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP44 IP65 With seal screw IP66 With seal screw IP67 With seal screw



Pushing Performance
Since 1945

Technical characteristics

Type rating acc. to UL 50 / UL 50E	4
	4X
	12

Material properties

Material (hood/housing)	Stainless steel
Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted
Material (seal)	FPM
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE
	DNV GL

Commercial data

Packaging size	1
Net weight	74 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140175617
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466