

## Han-INOX 3A-HBM-DL-C



Image is for illustration purposes only. Please refer to product description.

Part number	19 44 003 0306
Specification	Han-INOX 3A-HBM-DL-C
HARTING eCatalogue	<a href="https://harting.com/19440030306">https://harting.com/19440030306</a>

### Identification

Category	Hoods / Housings
Series of hoods/housings	Han-INOX®
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	 Straight With metal cover With seal

### Version

Size	3 A
Locking type	Single locking lever
Field of application	Hoods/housings for harsh environments
Details	for mounted female insert or for mounted Han-Brid® insert
Pack contents	With seal screw

### Technical characteristics

Tightening torque	1 Nm Fixing screws M3
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP44 IP65 With seal screw IP66 With seal screw IP67 With seal screw

## Technical characteristics

Type rating acc. to UL 50 / UL 50E	4 4X 12
------------------------------------	---------------

## Material properties

Material (hood/housing)	Stainless steel
Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted
Material (seal)	FPM
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel Naphthalene

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE DNV GL

## Commercial data

Packaging size	1
Net weight	73.8 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140163645
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466