Pushing Performance
Since 1945

Han INOX 3A-SMH-M20



Image is for illustration purposes only. Please refer to product description.

Part number	19 44 003 1150
Specification	Han INOX 3A-SMH-M20
HARTING eCatalogue	https://harting.com/19440031150

Identification

Category	Hoods / Housings
Series of hoods/housings	Han-INOX®
Type of hood/housing	Screw mounted housing

Version

Size	3 A
Version	Top entry
Number of cable entries	1
Cable entry	1x M20
Locking type	Single locking lever
Field of application	Hoods/housings for harsh environments
Pack contents	With seal screw 1x M20 stainless steel screw nut

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP44 IP65 With seal screw IP66 With seal screw IP67 With seal screw
Type rating acc. to UL 50 / UL 50E	4 4X 12

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Pushing Performance
Since 1945

Material properties

Material (hood/housing)	Stainless steel
Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
PFAS	No
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE UKCA DNV GL

Commercial data

Packaging size	1
Net weight	69.07 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140131958
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com